



- Ⓐ HOSE ASSY 04
PRESSURE
- Ⓑ .375" OD NYLON TUBING
RETURN
- Ⓒ AP4073 HOSE ASSY 04 x 60"
ROD END - ALWAYS PRESSURIZED
- Ⓓ AP8385 HOSE ASSY 05 x 60"
CAP END

NOTE: REFER TO COACH OEM INSTRUCTIONS FOR ALL WARNINGS AND OPERATION OF CHAIR.

NOTE: INSTALLATION MUST CONFORM TO GOOD SHOP PRACTICES, SAE STANDARDS, RVIA STANDARDS, AND OTHER APPLICABLE STANDARDS.

			HWH I-80 EXIT 267 SOUTH RT 1 MOSCOW, IOWA 52760		
			SCALE 1:6	DATE 14SEP20	DRAWN BY .
			HYD CONN DIAGRAM		
NO.	DATE	REVISION	NEWMAR		
THE INFORMATION DISCLOSED ON THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE DISCLOSED OR USED IN ANY MANNER WHICH WILL BE DETRIMENTAL TO THE HWH CORPORATION			DRAWING NUMBER MP71302		